



HERBEN VERTICAL 'SUPA' PERFORATING ARM for Heidelberg MO



Perforate, Slit or Score


Through the position of the trip cam, numbers, strike in blocks, or even full width imprint cylinders.

Pressure setting adjustable from the screw at the rear while your press is running; Anti-clockwise to increase pressure, see figure 1.



Blank-Out (Special Wheel)

Used in Conjunction with your Heidelberg Perforator you can blank out or iron the perforation flat, giving you an even stock thickness on delivery.



Setting-Up

Remove the tray before mounting this new 'SUPA' perforating arm.

It clamps on as the Heidelberg Perforating arm does.

Should the perforator wheel not reach on maximum adjustment or after sharpening unscrew the tension band at the head, withdraw the slide block and extend the adjusting pin by unscrewing 1 or 2 full turns & re-assemble.

